



Hello Fall

UPDATE REGARDING CHANGES TO VSP LAB NETWORK!!



As VSP has announced it's plans to significantly reduce their lab network nationwide, we want to reassure you that Interstate Lab Group remains fully committed to being your trusted business partner, maintaining the high standard of service you rely on.

Your success is our priority!

If you are currently a VSP One customer and considering a switch, we're here to make your transition seamless. Please reach out to your local Interstate sales consultant or call our customer service team at 800-472-5790 to start the process.

Shamir has expanded the availability of Shamir's Driver Intelligence Sun & Moon digital designs to now include Trivex materials. The Driver Intelligence Sun & Moon are unique digital lens designs, created exclusively to solve the challenges presented by any type of "Driver."



Updated Availability as of September 2024 (requires using Shamir SFSV blanks):

| | | DRIVE | | MATERIALS | Launching 9/3/24 |
|---------------|---|--------------|-----------------|--------------------|------------------|
| | | | | POLYCARBONATE 1.59 | Trivex 1.53 |
| PROGRESSIVE | Driver Intelligence™ SUN**** | POWER RANGE | -14.75 to +6.00 | | -10.00 to +6.00 |
| | MIN. FH (18MM) ADD power +0.75 to +3.50 | MAX CYLINDER | -7.00 | | -6.50 |
| | Prism up to 10.00 Diopters per quadrant | TREATMENT | C,P,BZ,TX | | C, P*, BZ, T, TX |
| PROGRESSIVE | Driver Intelligence™ MOON**** | POWER RANGE | -14.75 to +6.00 | | -10.00 to +6.00 |
| | MIN. FH (18MM) ADD power +0.75 to +3.50 | MAX CYLINDER | -7.00 | | -6.50 |
| | Prism up to 10.00 Diopters in each direction | TREATMENT | C,P,BZ,T,TX | | C*, P, BZ, T, TX |
| SINGLE VISION | Driver Intelligence™ SUN - SV**** | POWER RANGE | -14.00 to +6.00 | | -12.00 to +6.00 |
| | Fitting height needed Reference SV White Paper for details | MAX CYLINDER | -7.00 | | -6.50 |
| | Prism up to 10.00 Diopters in each direction | TREATMENT | C,P,BZ,TX | | C, P*, BZ, T, TX |
| SINGLE VISION | Driver Intelligence™ MOON - SV**** | POWER RANGE | -14.00 to +6.00 | | -12.00 to +6.00 |
| | Fitting height needed Reference SV White Paper for details | MAX CYLINDER | -7.00 | | -6.50 |
| | Prism up to 10.00 Diopters in each direction | TREATMENT | C,P,BZ,T,TX | | C*, P, BZ, T, TX |

LEGEND

- C CLEAR
- T TRANSITIONS® GEN 5™
- TX TRANSITIONS® XTRACTIVE® New Generation
- P POLARIZED
- BZ BLUE ZERO™
- * Preferred Treatment

Meet The People Who Make Up the Interstate Team!

Andy Eulett is a new customer service representative that has been employed with Interstate for two months at the Ohio location. In Andy's free time, he enjoys playing drums, spending time with his "kiddos," music, photography, and enjoying company with family and friends.

We are happy to have Andy as a member of our Interstate team!



Don't Forget to Text Us!



TEXT INTERSTATE LAB GROUP for QUICK Customer Service Assistance to 800-472-5790 (Mansfield) and 800-564-5546 (Indianapolis)!

Texting us provides a faster response time than calling in, with no time on hold and all conversations easily accessible in your texting app!

Text us for job status checks, remake requests and general questions.

The hours of operation for our texting service are the same as our customer service hours: **Monday-Friday, 8:00 am—5:30 pm.**